

## Chemetron Votator Scraped Surface Heat Exchangers

Mfg: Chemetron

Model: LS918B

Stock No. 300.140

Serial No. 82046VA

Chemetron Votator Scraped Surface Heat Exchangers. Model LS918B. S/N 82046VA. First tube left top to bottom: S/N A3939, Nat Brd no. 785. 2nd tube, right top: S/N A3940, Nat Brd no. 786. 3rd tube, bottom center: S/N B-677, Nat Brd No. B0677. (2) Stainless steel chrome plated barrels 6 in. diameter x 72 in. L, (1) barrel measuring 6 in. diameter x 48 in. L, rating: 400 psi at 375 °F, jacketed for 150 psi. Individual dimensions 15 in. W x 72 in. L. First tube, Model: 82046, S/N: A3939, Nat'l Bd: 785, Shell MAWP @ 375°F: 400 psi, Jacket MAWP @ 375°F: 150 psi. 2nd tube, Model: 82046, S/N: A3940, Nat Brd no. 786, Shell MAWP @ 375°F: 400 psi, Jacket MAWP @ 375°F: 150 psi. 3rd tube, Model: 82046V, S/N: B-677. Nat'l Bd: 763, Shell MAWP @ 300°F: 300 psi. Overall dimensions of frame 11 ft. L x 5-1/2 ft. W x 7 ft. H.



