

Cherry Burrell Mix and Blend Tank, 100 gallon, Reliance Duty Master Motor, 3/4 hp, 1,725 rpm, 208/230 volt, 2.8/3.0 amp, 60 hz, single phase, continuous duty. Tank is open top with bridge, coned bottom with 2 in. outlet and valve. Inside dimensions 28 in. diameter x 46 in. H, (4) 30 in. legs with wheels. Overall dimensions 31 in. L x 31 in. W x 85 in. H.

