

## Cherry Burrell Stainless Steel Refrigerated Tank-2, 000 Gallon

Mfg: Cherry Burrell

Model: FHW

Stock No. HDFI90.8

Serial No. 20-FHW-62-1594

Cherry Burrell Stainless Steel Refrigerated Tank- 2,000 Gallon. Model FHW, S/N 20-FHW-62-1594. Inside dimensions: 96 in. L x 84 in dia. Inlets: (1) 3 in., 8 in. window, 3 in. vent. Outlets: (1) 2 in. valve outlet with valve. (4) legs 6 in. H. Agitator; double spray balls. Shoemaker Electric. U.S. Syncrogear motor. Identification No. 11952. Frame 182 - 11. Type: JVNGWV. Rating 55 °C. 60 Hz, 460 V, 297 output torque in lbs. Gear ratio: 26.0. Motor: S/N 3264413, rpm 1800/900; 34/68 (final), 1/2/1/4 hp, 73 phase. Volt amps 1.24/1.25. Overall dimensions: 114 in. L x 90 in. W x 92 in. H.



