

## Thermal Care/Mayer Air-Cooled Accuchiller- 5.6 Ton

Mfg: Thermal Care/Mayer

Model: AQ0A0604

Stock No: RMCC348.5

Serial No: CH-95252

Thermal Care/Mayer Air-Cooled Accuchiller- 5.6 Ton. Model: AQ0A0604. S/N: CH-95252. Refrigerant: R-22. Heat transfer fluid: 30% Glycol. Maximum/minimum temperatures: 60/30 °F. Electrical requirements: 460 V, 17 FLA, 60 Hz, 3 phase. Compressor, Model: AG144UT-001, 5.5 hp. Evaporative condenser unit: 42 in L x 3 in. W x 25 in. H, 12 fins/inch, (2) condenser fans: 1/4 hp (each). Heat exchanger: 4 in. dia x 34 in. L. Feed tank: 18 gallon. Thermal Care/Mayer Process Pump, 1-1/2 hp, 3450/2850 rpm, 200-230/460 V, 5.6-5.6/2.8 amps, 60/50 Hz, 3 phase. Accuchiller series AQ are built for quiet performance. Inlet/outlet: 1-1/2 in. dia. threaded fittings. Overall dimensions: 60 in. L x 33 in. W x 54 in. H.



