

Waukesha Model 60 Positive Displacement Pump

Mfg: Waukesha

Model: 60

Stock No: OIP100

Serial No: 704 SS

Waukesha Positive Displacement Pump. Model: 60. S/N: 704 SS. Flow rate for new pump is 90 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. 316 Stainless steel pump body, cover and shaft. Maximum speed: 600 rpm. Features include: easy disassembly for cleaning, flexible three-way mounting, non-galling Waukesha "88" alloy rotors, and 3-A and BISCC approval. Inlets/outlets: (2) 2-1/2 in. dia. S-line fittings. Overall dimensions: 1 ft. 7-1/2 in. L x 10-5/8 in. W x 1 ft. 4 in. H.(ACN70).





