

Chester Jensen Falling Film Plate Chiller – 160 Tons

Mfg: Chester Jensen

Model:

Stock No: pBBCF158C.35

Serial No:

Chester Jensen Falling Film Plate Chiller. Cooling capacity: 160 tons at 256 gpm for a 26°F suction with a 15° TD. (8) plates with 36 corrugations each. Total cooling section area: 342 sq. ft. Plate dimensions: 5 ft. W x 3 ft. 9 in. H. MAWP: 200 psi @ 200°F. Reservoir capacity: 100 gallons; inside straight-wall dimensions: 7 ft. L x 3 ft. W x 8 in. H. Inlets: (1) 3 in. dia. refrigerant feed port. Outlets: (1) 4 in. dia. S-line drain port, (2) 3 in. dia. refrigerant suction ports. Overall dimensions: 9 ft. 4 in. L x 3 ft. 4-1/2 in. W x 5 ft. 1/2 in. H.

Plate S/N's: 36004, 37642, 37456, 37552, 37690, 37547, 37639, 37589. Nat'l Bd: 6955, 7989, 7855, 7925, 8024, 7920, 7986, 7952.



