

Grundfos Multi-Stage Centrifugal Pump

Mfg: Grundfos

Model: CRS-100 U-G-A-AUUF

Stock No. pHDHP142B.

Serial No. B 42006070E P1 9917

Grundfos Multi-Stage Centrifugal Pump. Model: CRS-100 U-G-A-AUUF. S/N: B 42006070E P1 9917. Capacity: 42 gpm @ 149 tdh. Maximum pressure: 335 psi. Maximum temperature: 250° F. Baldor Industrial Motor, 7-1/2 hp, 3450 rpm, 208-230/460 V, 19-17.2/8.6 amps. Inlets/outlets: (2) 2-1/2 in. dia. flanged connections. Overall dimensions: 12 in. L x 10 in. W x 42 in. H.

