

Gaulin MC45 Homogenizer

Mfg: Gaulin

Model: 2750 MC45 3TPS

Stock No. pHDM143.320

Serial No. 3797840

Gaulin MC45 Homogenizer. Model: 2750 MC45 3TPS. Micro gap. 3000 psi. Tapered seat poppet valve cylinders, spring loaded. Minimum capacity: 1700 gph. Maximum capacity: 4500 gph. Spare parts. S/N: 3797840. Overall dimensions: 92 in. L x 50 in. W x 64 in. H.

Leeson, ½ hp, 1725 rpm, 208-230/460 V, 3 phase, 2 & 1 FLA, 2.2 & 1.1 SFA. Uniclosed, 76 & 37-1/2 hp, 1800 & 900 rpm, 480 V, 94/65 amps, 60 cycles, frame: 405 U, ratio: 2:1, with a 20 in. fan in the belt. (2) Allen Brandley control valve system, maximum pressure: 300 psi, range: 0-150 psi. Inlets: 3 in. "S" line fitting, outlet: 2 in. "S" line. Oil inlets/outlets: (2) 1 in. converter to 3 in. threaded male.



