

1994 Chester Jensen Ammonia Plate Chiller

Mfg: Chester Jensen

Model: XB16-01-16-32

Stock No. pHMD467.68

Serial No. 9404-P

1994 Chester Jensen Ammonia Plate Chiller. Model: XB16-01-16-32. S/N: 9404-P. Chills liquid product instantly and continuously to 33°-34° F. Maximum flow rate per 32 corrugation section: 3,000 gph. (16) Plate sections. Standard section dimensions: 61-11/16 in. W x 43-1/8 in. H. Inlets: (1) 7 in. dia. port (product), (1) 5 in. dia. refrigerant feed pipe. Outlets: (1) 4 in. dia. refrigerant gas discharge pipe. 1994 Surge Tank- 150 Gallon. S/N: 43853. Nat'l Bd: 40959. MAWP @ 650 °F: 200 psi. MDMT @ 200 psi: -20 °F. Overall dimensions: 10 ft. 4 in. L x 86 in. W x 69 in. H.





