

Honeywell Temperature Control Panels and Chart Recorder

Mfg: Honeywell


Model:

Stock No. pRWGD260.3

Serial No.

Honeywell Temperature Control Panels and Chart Recorder.

Honeywell control panel: Control box off/on switch, 90-250 VAC, 50&60 Hz, 18 V. Operating temp: 32°F to 131°F. Bellofram air system, Input: 4-20 mA. Output: 3-15 psi. Supply: 18-100 psi. Digital controller with one button of function loup ½, lower display, manual auto, set point select. Inlets/outlets: (2) 1/8 in. air. Overall dimensions: 10-1/2 in. L x 17 in. W x 16 in. H.



Honeywell Control Panel. Honeywell control box. 90-250 V, 50&60 Hz, 18 VA. Ambient limits: 32°F to 131°F. Overall dimensions: 10-1/2 in. L x 12 in. W x 18-1/2 in. H.



Honeywell Circular Chart Recorder. Model: DR45AT-1100-001-0-000000-0. S/N: 0214Y254457100001. Control requirements: 120/240 VAC, 50&60 Hz, 20 VA, set 120 VAC, operating temp: 32°F to 131°F. Overall dimensions: 41 in. L x 12 in. W x 48 in. H.



