

## RayPack Hot Water Boiler

Mfg: RayPack

Model: H44001ACEDRCRA

Stock No. TLB01

Serial No. 9411119903

RayPack Hot Water Boiler Natl. Board No. 119903. Model H44001ACEDRCRA. S/N 9411119903. Input: 4,000,000 btu/hr, output: 3,280,000 btu/hr, max. water pressure 160 psi, min relief valve capacity: 3,280 lbs/hr, heating surface: 326 square feet, dimensions 104 in. L x 41 in. W x 68-1/2 H.

Category 1 Boiler	Natural Gas	LPG
Maximum Permissible Gas Supply Pressure	14 in. W.C.	14 in. W.C.
Minimum Permissible Gas Supply Pressure for purpose of input adjustment	7 in. W.C.	12 in. W.C.
Manifold Pressure	4 in. W.C.	11 in. W.C.

Minimum clearance from combustable construction: All Sides-24 in., top-24 in.  
For servicing provide at least 48 in. clearance in front of unit.

The Boiler Stack is in two sections. One 4 ft. high piece installed on the boiler and a 64 in. extension with a hat that bolts to the section in the boiler.

