

Horizontal Ammonia Recirculator- 5 ft. 1 in. dia. x 10 ft. 7 in. L.

Mfg:

Model:

Stock No. sEELD665.2a

Serial No.:

Horizontal Ammonia Recirculator- 5 ft. 1 in. dia. x 10 ft. 7 in. L. 1995 Cornell Centrifugal Pump, Model: 2CB-3-4, S/N: 91697, capacity: 25 gpm, working pressure: 25 psig. Baldor Electric Motor, 3 hp and 2 hp, 1760/1460 rpm, 230/460-190/380 V, 9/4.5-5.2/2.6 amps, 60/50 Hz, 3 phase. Cornell Centrifugal Pump, Model: 2CB-3-4. S/N: 72377. Marathon Electric Motor, 3 hp and 2 hp, 1735/1110 rpm, 230/460-190/380 V, 6.7/3.35-7.3/3.65 amps, 60/50 Hz, 3 phase. Refrigerating Specialty Co. Pressure Regulator, type: A4AK, range: 0-11 kg/cm² (0-150 psig). Inlets: (2) 8 in. dia. ports, (1) 6 in. dia. port, (1) 1-1/2 in. dia. port. Outlets: (1) 2 in. dia. port, (3) 3/4 in. dia. ports, (1) 1-1/2 in. dia. FNPT fitting, (3) 1-1/4 in. dia. ports. Overall dimensions: 11 ft. 3 in. L x 7 ft. W x 8 ft. 10 in. H.









