

Waukesha U-30 Positive Pump

Mfg: Waukesha

Model: U-30

Stock No. tGHFI06.

Serial No. 13266 SS

Waukesha U-30 Positive Displacement Pump. S/N: 13266 SS. Single mechanical seals. Displacement per revolution: 0.060 gal. Maximum capacity: 25.98 gpm. Minimum capacity: 2.88 gpm. Reliance Electric Motor, 2 hp, 1725 rpm, 208-230/460 V, 6.4-6.4/3.2 amps, 60 Hz, 3 phase. Reeves Vari-Drive, 9.7 ratio, 433 rpm (max), 48 rpm (min). Inlets/outlets: (2) 1-1/2 in. dia. threaded fittings. Overall dimensions: 33 in. L x 24 in. W x 25 in. H.

