

Unused Chemetron Corp. (Waukesha Cherry-Burrell) Votator with Surge Tank – 6 in. x 72 in.

**Mfg: Chemetron Corp.
(Waukesha Cherry-Burrell)**

Model:

Stock No: tLDF01

Serial No: A2857

Unused Chemetron Corp. (Waukesha Cherry-Burrell) Votator. S/N: A2857. Natl. Bd: 4480. Product contact surface material(tube): chrome-plated nickel. Stainless steel grade: 304. Inner shell maximum working pressure: 250 psi. at 375°F. Jacket maximum working pressure: 150 psi at 375°F. Votator shaft: 7 ft 10-1/2 in. L., scrapers: 6-1/8 in. x 1-5/8 in. Votator barrel inside dia. 6-1/8 in. Reliance electric motor: ID no: P25G16970-GS-GZ, 15 HP, type P, insulation class: B, 1765 rpm, 230/460 volts, 40/20 amps., 60 Hz., 3 phase. Reliance Master XL gear motor: ID No. 497652-KZ, size 254DG38A2 ratio 7.6:1. Surge tank: S/N: 1067. Natl. Bd 4586, approximate capacity: 40 gallons. Surge tank dimensions: 18 in. dia. x 32-3/4 in. straight wall. Overall dimensions: 7 ft. 9-1/2 in. L x 31 in. W. Overall dimensions: 12 ft. 5 in. L x 3 ft. 4-1/2 in. W x 4 ft. 7 in. H.









