Krones 20 Valve Filler with Alcoa Capper	
Mfg: Krones	Model: 8402
Stock No: 2000.BP2a	Serial No: 120284

Krones 20 Valve Filler with Alcoa Capper. Model: 8402. S/N 120284. Fills from 0.5 liter @ 280 BPM up to 3 liter @ 180 BPM. Pressurized filler with 20 valves. Distance between valves: 7-5/16 in. Hopper: 19-3/4 in. dia. x 18-1/2 in. H. Dynamatic Motor: 10 hp, 1,745 rpm, 230/460 V, 27.8-13.6 amps, 60 Hz, 3 phase. Ajusto Speed Motor Drive: 1,710/175 max/min rpm, 45 V DC, 2.96 amps. ZAE D-2000 Hamburg 50 Motor Drive: 10:1 ratio. Antriedstechnik Motor: 1,350-1,420/1,680-1,720 rpm, 346-240/380-460 V, 0.83-1.44/0.7-1.2 amps, 50/60 Hz. Lenze Motor Drive. Inlets/outlets: (1) 1 in. dia. pipe, (1) 1 in. dia. male ferrule, (2) 1-1/2 in. dia. threaded fitting, (1) 2-1/2 in. dia. threaded fitting. Overall dimensions: 130 in. L x 90 in. W x 108 in. H.

Alcoa Capper, 5 head, set up for ROPP caps. Change parts for magnetic chucks available upon request.

















































































