

Russell Air Cooled Condenser – 40 Tons

Mfg: Russell

Model: VAC-55

Stock No. HDBD143.1

Serial No. H936C0011

Russell Air Cooled Condenser. Model: VAC-55. S/N: H936C0011. Approximate Capacity: 40 tons. Refrigerant: R22, water, glycol. Airflow: 31000 cfm. Design pressure: 380 psig. Number of fans: 3. Fan diameter: 2 ft. 5 in. dia. (3) Marathon Electric Motors, 1-1/2 hp, 1140 rpm, 208-230/460 V, 5.45-5.4/2.7 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. dia. port. Outlets: (1) 1 in. dia. port. Overall dimensions: 13 ft. 9 in. L x 4 ft. W x 3 ft. 8 in. H.



