

Vilter VMC 450 8-Cylinder Reciprocating Compressor - 125 HP

Mfg: Vilter

Model: VMC 450

Stock No: AANF299

Serial No: 60360

VMC 45L 8-Cylinder Reciprocating Compressor with 125 HP motor. Model: 458. S/N: 60360. Order No.: F-29251. Size: A10K458B. High/Low Pressure: 575/375 PSI. Vilter 4 in. and 5 in. valves. Compressor weight less motor: 3,400 lbs. Oil Cooler Size 3-Y-12, Type MVHT-4-A-0T, Shell Design Pressure: 300 PSI at 300 F, Tube Design Pressure: 300 PSI at 300F, Serial No.: WT-46615/49, 1986. Lincoln Motor 125 HP, 1770 RPM, 230/460 Volts, 288/144 Amps, 3-phase, 60 Hz, 405T Frame, Can be used on 208V system up to 330 Amps. Allen-Bradley SMC-Flex Starter Catalog no. 150-F201FDB, 480V Line Voltage, 3-phase, 60HZ, Type 4, 150 HP, 201 Amp, 120V Control Voltage, year 2007. Overall dimensions: 75 in L x 48 in. W x 56 in. H.







