

Grundfos / Paco Pumps Centrifugal Pump

Mfg: Grundfos / Paco Pumps

Model: 40955

Stock No: ACEU77

Serial No: KRB47091B

Grundfos / Paco Pumps Centrifugal Pump. Model: 40955. S/N: KRB47091B. Flow rate for new pump is 1200 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 9-1/2 in. Baldor Industrial Motor, 15 hp, 1760 rpm, 208-230/460 V, 41-38/19 amps, 60 Hz, 3 phase. Inlet: (1) 5 in. dia. flanged port. Outlet: (1) 4 in. dia. flanged port. Overall dimensions: 4 ft. 1 in. L x 1 ft. 4 in. W x 1 ft. 7 in. H. (ACN33).





SPEC.	37F599T867H1		
HP	15		
VOLTS	208-230/460		
AMPS	41-38/19		
R.P.M.	1760		
FRAME	254T	HZ	60
SER. F.	1.15	CODE J	DES A
NEMA NOM. EFF.	91	%	P.F.
RATING	40C AMB-CONT		
CC	010A	USABLE AT 208V	
BEARINGS	DE 6309	ODE 62	
ENCL	OPSB	SN	F061115091
MFG. BY BALTOR ELECTRIC			

11409557462011822
 KRB47091B
 490 75