

Krack DTX-Series Hot Gas Defrost Ammonia Evaporator- 15.25 Tons

Mfg: Krack

Model: DTX6S-1530-RBA-HGU-LH

Stock No. ASLC027.

Serial No. 447731-03A

Krack DTX-Series Hot Gas Defrost Ammonia Evaporator- 15.25 Tons. Model: DTX6S-1530-RBA-HGU-LH. S/N: 447731-03A. Capacity: 183,000 Btuh. Airflow: 27,000 cfm. Nominal fin spacing: 4 fpi. Heat transfer surface area: 3,720 sq. ft. Suction temperature: +20 °F. Room temperature: +32 °F. Steel tubes and fins. Recirculated bottom. hot gas coil and pan. DTX-Series units can be used in medium and low temperature holding coolers, freezers, shipping dock, carcass chill, assembly and process areas. (6) Franklin Electric Motors, 1/3 hp, 1140/950 rpm, 208-230/460 V, 60/50 Hz, 3 phase. Inlets: (1) 1 in. dia. port. Outlets: (1) 2-1/2 in. port. Overall dimensions: 13 ft. 2 in. L x 38 in. W x 53 in. H.



