

H. Maurer+Sohne External Sawdust-Fired Smoke Generator- 70 Gallon

Mfg: H. Maurer+Sohne

Model: Goliath I

Stock No. BAFB114.1a

Serial No.

H. Maurer+Sohne External Sawdust-Fired Smoke Generator- 70 Gallon. Model: Goliath I. Pump with Lafert Motor, 3/4 hp, 3170 rpm, 373/575 V, 1.8/1 amps, 60 Hz, 3 phase. Bottom sweep agitator: 23 in. dia. Motor, 0.33 hp, 575 V, 0.6 amps, 60 Hz. German Sawdust-fired smoke generator for open and exhaust gas reducing plants. Infeed: 61 in. H, Outlet: 6-1/2 in. dia. Overall dimensions: 36 in. L x 29 in. W x 77-1/2 in. H.



