

APV HTST Skid with Titanium Plates

Mfg: APV

Model: SR-35

Stock No. BIIR05.

Serial No. 16032

APV HTST Skid with Titanium Plates. Model: SR-35. S/N: 16032. APV Heat Exchanger: (55) Titanium plates. (2) divider plates. Heat transfer surface area: 235.27 (approx.). Holding tube diameter: 2 in. Capacity: 2-1/2 gal. Heat transfer surface area: 8 sq. ft. (approx.). Carver Centrifugal Pump, Type: 2.5x2x7LA-33D, S/N: 82861, 3450 rpm (final), impeller diameter: 5-1/2 in. Baldor Industrial Motor, 5 hp, 3450 rpm, 208-230/460 V, 13.2-12/6 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. S-line fitting, (1) 3 in. dia. with a 7 in. dia. flange and (4) 3/4 in. dia. attachment holes at a center-to-center distance of 6 in. Outlets: (1) 3 in. dia. S-line fitting, (2) 3 in. dia. with a 7 in. dia. flange and (4) 3/4 in. dia. attachment holes at a center-to-center distance of 6 in. Overall dimensions: 9 ft. 10 in. L x 68 in. W x 95 in. H.



