

McBrady Orbit Cleaner-Rinser

Mfg: McBrady

Model: 200

Stock No. 120.BP7

Serial No. A48-2484

McBrady Orbit Cleaner-Rinser. Model: 200. S/N: A48-2484. 18-Nozzle rotor. Maximum bottle size: 3 in. dia. x 6 in. H. Current set-up: 16 oz. bottles. Maximum bottle neck diameter: 3 in. US Motor, 1 hp, 1730 rpm, 230-460 V, 60 Hz, 3 phase. US Varidrive Module. Overall dimensions: 71 in. L x 47.5 in. W x 87 in. H. Air cleaning is performed through a direct tube, injected inside the each container or vial. Conveyor infeed/exit height: 37 in. Inlets: (1) 1/4 in. dia. port, (1) 3 in. dia. port. Outlets: (3) 1/8 in. dia. spray jets, (1) 3 in. dia. port. Overall dimensions: 82-1/2 in. L x 48 in. W x 85 in. H.



