

Graseby Soft Start Motor Starter – 200 HP

Mfg: Graseby



Model: PL200V4B3G

Stock No: BZCH508.5a

Serial No: 95063005D

Graseby Soft Start Motor Starter – 200 HP. Model: PL200V4B3G. S/N: 95063005D. Input: 460 V, 270 amps, 60 Hz, 3 phase. Output: 460 V, 270 amps, 60 Hz, 3 phase, 150 KW. Overall dimensions: 2 ft. 6-1/4 in. L x 1 ft. 3 in. W x 3 ft. 2 in. H.





GRASEBY		GREENSBORO	
CONTROLS		NORTH CAROLINA	
MODEL: PL200V4B3G	HP: 200		
S/N: 95063005D	KW: 150		
INPUT: 460 V	270A	3 PH	60 HZ
OUTPUT: 460 V	270A	3 PH	60 HZ

