

## Moyno Progressing Cavity Pump

Mfg: Moyno

Model: 1TL10H SSQ

Stock No. CCFP148.

Serial No. 012449

Moyno Progressing Cavity Pump. Model: 1L10H SSQ. S/N: 012449. With 304 stainless steel suction housing, 316 stainless steel internal components, and a nitrile rubber stator. Capacity: 115 gpm @ 40 psi. U.S. Motor Unimount 125, 7.5 hp, 1,745 rpm, 230/460 V, 20.6/10.3 amps (25.0/12.5 S.F. amps), 60 Hz, 3-phase. U.S. Motors Varidrive Module, 10 hp max input at 1,750 rpm, 450/3,600 min/max rpm, 335 in-lbs max output torque. U.S. Motor Drive, no nameplate information. Inlets/outlets: (1) 6 in. dia. inlet with 11 in. dia. flange, (8) attachment holes; (1) 6-1/4 in. dia. outlet with 11 in. dia. flange and (8) attachment holes. L. amps (25.0/12.5 S.F. amps), 60 Hz, 3-phase. U.S. Motors Varidrive Module, 10 hp max input at 1,750 rpm, 450/3,600 min/max rpm, 335 in-lbs max output torque. U.S. Motor Drive, no nameplate information. Overall dimensions: 111 in. L x 21 in. W x 40 in. H.



