

Goulds 3196 Centrifugal Pump

Mfg: Goulds

Model: LF3196

Stock No: CCFP160A

Serial No: 745E096

Goulds Centrifugal Pump. Model: LF3196. S/N: 745E096. Size: 1X2-10. Flow rate for new pump is 60 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 8.87 in. John Crane seals. 316 stainless steel base. Maximum design working pressure: 250 psi @ 100 °F. U.S. Electric Motor, 20 hp, 3500 rpm, 230/460 V, 17.2/23.6 amps, 60 Hz, 3 phase. Inlet: (1) 2 in. dia. flanged port. Outlet: (1) 1 in. dia. flanged port. Overall dimensions: 4 ft. 10 in. L x 2 ft. W x 2 ft. 4-3/4 in. H.









