

## Foxboro Electronic Differential Pressure Transmitter

Mfg: Foxboro

Model: 832DP-I3S1SH0

Stock No. CG-MM484A.0

Serial No. 92441367

Foxboro Electronic Differential Pressure Transmitter. Model: 832DP-I3S1SH0. S/N: 92441367. Output: 4-20 mA (dc); 10-50 mA (dc). Range: 0-5 to 0-750 in H<sub>2</sub>O. Accuracy: 4-20 mA and 10-50 mA: +/-0.20% of calibrated span. Intelligent digital: +0.07% of calibrated span. Intelligent, 4-20 mA: +/-0.10% of calibrated span. Power: 4-20 mA, 12.5-65 Vdc; 10-50 mA, 30-95 Vdc. Intelligent digital: Fieldbus Module (FBM) 18 Intelligent, 4-20 mA: 16.5-42 V dc. The 823DP Electronic Differential Pressure Transmitters measure differential pressure and transmit a proportional electrical signal. Overall dimensions: 6 in. L x 6 in. W. X 9 in. H.

