

## Kontro Sine MR 130 Cavity Pump

**Mfg: Kontro Sine**

**Model: MR130NNTC**

**Stock No: CHBR01.12**

**Serial No: 209985130A467**

Kontro Sine Cavity Pump. Model: MR130NTCC. S/N: 209985130A467. Sine pumps are designed for use in the food processing industry for pumping products with soft solids. Soups, sauces, frozen foods, salads, and meat mixes are commonly used with the Sine pump. It has low shear product handling and is commonly used for feeding a filler machine. The MR series has a 3-A Sanitary rating, low pulsation, and good inlet suction. Max Capacity of 99 gpm at max speed of 800 rpm. Inlets/Outlets: 3 in. Tri-clamp style fittings. Stainless steel head. Reeves variable speed drive: 10 hp, 230/460 V, 26/13 amps, 60 Hz, 3 phase, 1740 rpm. Measured rpm output: 265 min, 1035 max. Overall dimensions: 6 ft. 1 in. L x 2 ft. 8 in. W. x 3 ft. 1 in. H. (ACN167).







