Vilter 440 Series 8-Cylinder Reciprocating Compressor - 125 HP	
Mfg: Vilter	Model: 448
Stock No.: DBPC042	Serial No.: 22903

Vilter 440 Series Reciprocating Compressor. Model: 448. Serial 22903. Order: F-27760. Size: A12K448. Number of cylinders: 8. Displacement: 182 CFM. Nominal ratings: 94 TR at +20F / +95F (R-22 freon); 93 TR at +20F / +95F (R-717 ammonia). Pacemaker motor: 125 HP, 1780 RPM, 460V, 3-phase, 60 Hz. Compressor weight: 3400 lbs. Ports (suction/discharge): 4 in. / 3 in. Previously used with ammonia refrigerant.











