

Sine Positive Displacement Pump

Mfg: Sine

Model: MR135 NNRBS A590

Stock No. DBPF2109.12

Serial No. 95710244

Sine Positive Displacement Pump. Model: MR135 NNRBS A590. S/N: 95710244. Capacity: 98.73 gpm. Pump maximum capacities: 400 gpm at a speed range of 600 rpm this will pump a total distance of 347 ft. Maximum working pressure: 150 psi. Temperature range: -40 to 300°F. Single stage. Baldor Industrial Motor, 10 hp, 1760 rpm, 208-230/460 V, 28.5-28.4/14.2 amps, 60 Hz, 3 phase. Motor drive, ratio: 4.1, final speed: 429.26 rpm. The MR135 is a medium duty sanitary pump. Typical applications: cheese, curd, cottage cheese, yogurt, concentrates, beer, yeast, batter, fillings, stews, deli salads, chocolate, and caramel. Pump inlet: 9 in. L x 2-1/2 in. W. Outlet: 3 in. threaded (male). Overall dimensions: 31 in. L x 36 in. W x 19 in. H.





