

## Raque In-Line Pneumatic 4 Piston Filler

Mfg: Raque

Model:

Stock No. 55.DBSa.28

Serial No.

Raque In-Line Pneumatic 4 Piston Filler. Stainless Steel. (4) Feeding pistons: 2 in. dia. x 2-1/4 in. stroke. Valve diameter: 1 in. Center between valves: 2-1/4 in. minimum. Maximum filler volume: 0.125 liters. Capacity: 26 bpm. Bottle dimensions: 2-1/4 in. W x 2-1/2 in. H. Transmission: 0.5 hp, 230 V. Tank volume: 85 liters. Conveyor chain: 3-1/4 in. Overall dimensions: 64 in. L x 52 in. W x 82 in. H. EXR

