

1996 Frick Reciprocating Compressor Package

Mfg: Frick

Model: HCL060757UB16

Stock No: DFMT01

Serial No: 26727601-9706-20

1996 Frick Reciprocating Compressor Package. Type: HCL 6075. Sales order no: 26727601. Serial nos. 82-015-5020-252, 26727601-9706-20. National Board. no. 34762. Refrigerant: ammonia (R-717). Set up for low temperature application, 6 cylinder compressor, .075 mm bore, belt driven. Toshiba Ram motor: serial no. 7006708-01-TZ. 20 hp, 230/460V, sf: 1.15, 50/25 amps, 60 Hz, 3 phase. Pressure vessel: MAWP: 300 psi at 200°F, MDMT: -20°F @ 300 psi psig. Respective high and low pressures: 360/260 psig. Features separate dial gauges for oil, suction and discharge pressure, Cyrus Shank Company safety relief valves, Danfoss pressure controls, and Armstrong floating lever liquid drainers. Compressor run time: 30100 hours. Overall dimensions: 7 ft. 4 in. L x 4 ft. 2 in. W x 6 ft. 11 in. H.





