


NOT USED ON 15 GAL. TANKS AND ONLY USED WHEN TWO FLOAT SWITCHES ARE REQUIRED.

USED ON 15 GAL. RECEIVER WHEN TWO FLOAT SWITCHES ARE REQUIRED.

RECOMMENDED DISCHARGE NOZZLE SIZE	CAPACITY CHART
0-15	3/4"
16-60	1" OR 1 1/2"
61-113	2"
114-150	2 1/2"
151-250	3"
251-400	4"

BUTTERFLY VALVE THICKNESS	
3" VALVE	1 1/2"
4" VALVE	2"

4" BUTTERFLY VALVE ONLY USED ON 114 & 129 130 GPM PLUS AND 131 PUMPS



REC.	SIZE	THICK	A	B	C	D	E	F	G	H	J	K	L	M	DRAIN
15 GAL.	16 x 16 x 13	3/16	2	1 1/4	1 1/4	11 1/8	1 3/4	10 15/16	4 3/4	11 5/8	7 1/4	17 7/8	23	43	1/2
21 GAL.	18 1/4 x 18 1/4 x 15 1/4	3/16	2	1 1/4	1 1/4	13 3/8	1 3/4	13 3/16	4 3/4	13 7/8	7 1/4	20 1/8	24 3/4	45	1/2
35 GAL.	20 1/4 x 20 1/4 x 20 1/4	3/16	3	1 1/2	1 1/2	17 1/2	2 7/8	17	7 1/8	18	10 1/8	22 1/8	26 3/4	50	1/2
45 GAL.	24 1/4 x 24 1/4 x 18 1/4	3/16	3	1 1/2	1 1/2	15 1/2	2 7/8	15	7 1/8	16	10 1/8	26 1/8	30 3/4	48	1/2
60 GAL.	24 1/4 x 24 1/4 x 24 1/4	3/16	3	1 1/2	1 1/2	21 1/2	2 7/8	21	7 1/8	22	10 1/8	26 1/8	30 3/4	54	1/2
81 GAL.	30 1/4 x 30 1/4 x 21 1/4	3/16	4	2	2 1/2	18 1/2	3 1/2	18	9 1/8	19	13 5/8	32 1/8	36 3/4	51	1/2
128 GAL.	31 3/8 x 31 3/8 x 31 3/8	3/16	4	2	2 1/2	28 1/8	3 1/2	27 3/8	9 1/8	28 3/4	13 5/8	33 1/4	37 7/8	61	3/4
168 GAL.	36 3/8 x 36 3/8 x 30 3/8	3/16	4	2 1/2	2 1/2	27 1/8	3 1/2	26 3/8	9 1/8	27 3/4	13 5/8	38 1/4	42 7/8	60	3/4
235 GAL.	38 3/8 x 38 3/8 x 38 3/8	3/16	4	2 1/2	2 1/2	35 1/8	3 1/2	34 3/8	9 1/8	35 3/4	13 5/8	40 1/4	44 7/8	68	1"

"X" DIMENSION						
PUMP MODELS						
110	106	113, 116 & 127	117 & 121	114 & 129 UNDER 130 GPM	114 & 129 130 GPM & OVER	131
3.13	3.31	4.19	3.82	4.50	6.32	7.00

TYPE DS & LPC & PS FLOOR-MOUNTED STEEL RECEIVER W/ CONDENSATE PUMPS

DRAWN BY: C. REED DATE: 4/04 REVISION: .9

DIMENSION PRINT: 40007

SHIPCO® PUMPS

MANUFACTURED BY
SHIPPENSBURG PUMP COMPANY INC.
P.O. Box 279 Shippensburg, Pa. 17257
PHONE 717 532-7321 / FAX 717 532-7704
WWW.SHIPCOPUMPS.COM

SHIPCO® IS A REGISTERED TRADEMARK OF SHIPPENSBURG PUMP CO., INC.