

2000 Buffalo Pumps Can-O-Matic II Ammonia Pump

Mfg: Buffalo Pumps

Model: HCR Can-O-Matic II

Stock No: DNBA096

Serial No: 00440850-001

2000 Buffalo Pumps Can-O-Matic II Ammonia Pump. Model: HCR Can-O-Matic II. Size: 3x2x13. Flow rate for new pump is 300 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 13 in. Motor: 10 hp, 1750 rpm, 460 v, 15.5 a, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. flanged port. Outlets: (1) 2 in. dia. flanged port. Overall dimensions: 2 ft. L x 2 ft. W x 2 ft. H.(ACN76a).







MODEL NO. 3X2X13-10HP
SERIAL NO. 00440850-001 120 165

VOLTS 215V
AMPS 15.5

PHASES 3
SPEEDS 1750 60

CONT. 115-115-115-0
DANGER

MADE IN U.S.A.