

MBC Single Pass, Variable Speed Hot Water Blancher

Mfg: MBC

Model:

Stock No. DSBI067.7

Serial No.:

MBC Single Pass Variable Speed Hot Water Blancher. Stainless steel tank: 235 gal. 380,000 BTU/hr. 380 lbs steam/hr. 11 boiler hp. (2) Stainless steel mesh belts. Lower belt: 20 ft. L x 13 in. W. Upper belt: 18-1/2 ft. L x 13 in. W. Mesh size: 2-1/2 in. L x 1/2 in. W. Baldor Motor: 1/2 hp, 1,725 rpm, 230/460 V, 1.6/0.8 amps, 60 Hz, 3 phase. General Electric motor: 1/2 hp, 1,725 rpm, 115/230 V, 1 phase. Emerson Horizon 1 speed control. Chain lift, cover lift, and conveyor lift. Overall dimensions: 20 ft. 6 in. L x 40 in. W x 7 ft. 2 in. H.



