

1995 Comec Vertical Stainless Steel Micro Ball Mill

Mfg: Comec

Model: M100

Stock No. DSVT029.2a

Serial No.:

1995 Comec Vertical Stainless Steel Micro Ball Mill. Type: M100. Mat: 6983. ABB motor, 20 hp (20.11 Kw), 1740 rpm, 60 Hz, 440 V & 40 amps, 440 V & 34 amps. Stainless steel double wall tank: 25 gallon (100 liter). Useful capacity: minimum 8 gal. (30 liters); maximum 23.5 gal. (90 liters). Ball charge: 44 lbs (20 Kg). (2) Grinder discs: 10 in. diameter. Pressure cover: 20 in. diameter, additional opening: 8 in. diameter. Control box. Manual switch controller: electric tripping, slow speed, fast speed, stop. Tank opening: 1 in. threaded male, valve. Overall dimensions: 52-1/2 in. L x 23-1/2 in. W x 69 in. H.





