

Stainless Steel Mix Tank- 1000 Gallon

Mfg:

Model:

Stock No. DTTC2033.

Serial No.:

Stainless Steel Mix Tank- 1000 Gallon. Inside straightwall dimensions: 6 ft. L x 5 ft. 3 in. W x 4 ft. 11 in. H. ProQuip Z-Series Agitator Drive, Model: ZG-7, S/N: 15647GR, 7 ratio, 168.5 rpm (final), 36 in. dia. agitator. Baldor Industrial Motor, 15 hp, 1180 rpm, 460 V, 18.7 amps, 60 Hz, 3 phase. Inlets: (1) 1 in. dia. S-line fitting (sprayball), (3) 2-1/2 in. dia. S-line fittings (product), (7) 3 in. dia. S-line fittings (product). Outlets: (1) 20 in. W x 2 in. H overflow port, (1) 4 in. dia. bevel with hex, (1) 8 in. dia. discharge port, (1) 20 in. W x 25 in. H discharge port. Overall dimensions: 10 ft. 3 in. L x 6 ft. 9 in. W x 8 ft. 7 in. H.



