

Avery WeighTronix Low Profile Floor Scale with Roller Conveyor

Mfg: Avery WeighTronix

Model: LPFS10

Stock No. DTTC2052.

Serial No. 2767

Avery WeighTronix Stainless Steel Platform Scale with Roller Conveyor. Model: LPFS10. S/N: 2767. Capacity: 5,000 lbs. Weigh-Tronix Weigh-Bars, Model: WBP -5.00K, Class: III. Safe load limit: 10,000 lbs. Stainless Steel Roller Conveyor- 78 in. x 42 in., (10) 5-1/2 in. dia. x 3 ft. 3 in. L rollers. Baldor Industrial Motor, 2 hp, 1750 rpm, 230/460 V, 5/2.5 amps, 60 Hz, 3 phase. Baldor Industrial Drive, ratio: 50, 35 rpm (final). Roller conveyor infeed/exit height: 2 ft. 7 in. H. Avery Weigh Tronix low profile scales are designed with the user in mind. The shallow 3.5° ramp incline and low deck height make getting on or off easy for small fork lift trucks and hand trucks, translating into increased productivity, increased frequency of units weighed, and a safer working environment for employees. Overall dimensions: 7 ft. 4 in. L x 6 ft. 1 in. W x 4 ft. 5 in. H. (ACN160).



