


Stainless Steel Hydraylic Power Pack

Mfg:	Model:
Stock No. DTTC2076.	Serial No.:

Stainless Steel Hydraylic Power Pack. Food grade hydraulic oil only. Stainless Steel Oil Reservoir Tank-170 Gallon. Inside straightwall dimensions: 3 ft. 10 in. L x 2 ft. W x 3 ft. H. Oil Gear Hydraulic Pump, Model: PVW34DL SAY CN. S/N: 89039663. Baldor Electric Motor, 20 hp, 1760 rpm, 208-230/460 V, 54-50/25 amps, 60 Hz, 3 phase. Oil Gear Hydraulic Pump, Model: PVWH15CNN, S/N: 99363774. Baldor Electric Motor, 10 hp, 1725 rpm, 208-230/460 V, 28-26/15 amps, 60 Hz, 3 phase. Oil Gear Hydraulic Pump, Model: PVWHL SAYC NNN, S/N: 01448272. Baldor Electric Motor, 10 hp, 1760 rpm, 230/460 V, 25/12.5 amps, 60 Hz, 3 phase. Hydraulic Pump, Model: PVWH10LSAYC NNN, S/N: 00410558. Baldor Electric Motor, 5 hp, 1750 rpm, 230/460 V, 13.4/6.7 amps, 60 Hz, 3 phase. B&F Hydraulic Pump, Model: ss-1102-210-X-5.81, S/N: 14412-2. American Industrial Oil Cooler, Model: AC-35-1, S/N: 34366A, temperature: 400 °F, pressure: 300 psi. Reliance Electric Motor, 1.5 hp, 1725 rpm, 208-230/460 V, 4.4/2.2 amps, 60 Hz, 3 phase. (6) Vickers Directional Valves, S/N's: 879135DG4S4012CB60, 879135DG4S4012CB60, DG4V3S2GMB560, DG4V32CMFTWB660. Overall dimensions: 8 ft. 7 in. L x 5 ft. 3 in. W x 7 ft. 5 in. H.







**FOOD GRADE
HYDRAULIC OIL
ONLY**