

Stainless Steel Hydraulic Power Pack


Mfg:


Model:

Stock No. DTTC2077.


Serial No.:



Stainless Steel Hydraulic Power Pack. Food grade hydraulic oil only. Stainless Steel Reservoir Tank-170 Gallon. Inside straight-wall dimensions: 3 ft. 10 in. L x 2 ft. W x 3 ft. H. Oil Gear Hydraulic Pump, Model: PVWH34LSAYCNNN, S/N: 94167190. Baldor Electric Motor, 20 hp, 1760 rpm, 208-230/460 V, 54-50/25 amps, 60 Hz, 3 phase. Oil Gear Hydraulic Pump, Model: PVWH15LSAYCNNN, S/N: 98339105. Baldor Electric Motor, 10 hp, 1760 rpm, 208-230/460 V, 28.5-28.4/14.2 amps, 60 Hz, 3 phase. Oil Gear Hydraulic Pump, Model: PVWH15LSAYCNNN, S/N: 92121290. Baldor Electric Motor, 10 hp, 1760 rpm, 208-230/460 V, 28.5-28.4/14.2 amps, 60 Hz, 3 phase. Oil Gear Hydraulic Pump, Model: PVWH10LSAYCNNN, S/N: 19373416. Reliance Electric Motor, 5 hp, 1750 rpm, 230/460 V, 12.2/6.1 amps, 60 Hz, 3 phase. Americal Industrial Oil Cooler, Model: AC-35-3, S/N: 34520A, temperature: 400 °F, pressure: 300 psi. Vickers Directional Valves. Model No's: 879135DG4S4012CB60, 02120015DG4S4W012CB60, DG4V3S2CMFWB560, KFDG4V32C28SMV1H620, DG4V3S2CMFWB560, KFDG4V32C285ZMV1H620. Overall dimensions: 8 ft. 7 in. L x 5 ft. 3 in. W x 7 ft. 5 in. H.














**FOOD GRADE
HYDRAULIC OIL
ONLY**

VICKERS
DIRECTIONAL VALVE

PILOT VALVE MODEL NO.
02-120015 D/4S4W 012C B 60
SEE MAINSTAGE NAMEPLATE FOR
TWO-STAGE VALVE MODEL NO. 100S
VICKERS, INC.
A TRINOVAT COMPANY. MADE IN THE U.S.A.