

## Rexnord Right Angle Drive

Mfg: Rexnord

Model:

Stock No. DTTC2103.

Serial No. 33448392-01WH

Rexnord Right Angle Drive. S/N: 33448392-01WH. Type: H. Size: 145. Assembly: 1B. Input: 6.65/1750 rpm. Output: 17906 in./lb. Shaft diameter: 2-3/8 in. Sprocket diameter: 10-1/2 in. Number of teeth: 25. Pitch: 1-1/4. Baldor Electric Motor, 5 hp, 1750 rpm, 208-230/460 V, 13.8-13.4/6.7, 60 Hz, 3 phase. Overall dimensions: 3 ft. 7 in. L x 2 ft. 3 in. W x 1 ft. 11 in. H.



