

FES 775 / Mycom 320-SU-LX Booster Rotary Screw Compressor Package – 250 HP

Mfg: FES / Mycom

Model: 775 / 320 SU-LX

Stock No: DTTC807.

Serial No: 3251382

FES 775 / Mycom 320-SU-LX Booster Rotary Screw Compressor Package. Model: 775 / 320 SU-LX. S/N: 3251382. Refrigerant: last used with R-717 (ammonia). Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. Nominal capacity: 254.0 Tons at 255.0 bhp with a -35°F suction temperature and a 20°F discharge temperature. Bhp per ton: 1.000. Displacement: 2,230 cfm. FES oil separator, S/N: 81280, National Board: 1366, MAWP: 250 psi at 300 °F to -20 °F. Head radius: 2:1. Head thickness: 0.375 in. Shell thickness: 0.375 in. Toshiba motor, 250 hp, 3540 rpm, 4160 V, 58/32 amps, 60 Hz, 3 phase. Viking rotary pump, Model: AK 28A, S/N: 1008100. Mycom Mypro-M control panel. Outlet: 4 in. dia. refrigerant discharge. Overall dimensions: 15 ft. 5 in. L x 4 ft. 9-1/2 in W x 7 ft. 4 in. H. (SR500) (ACN1450)







