

FES 775 / Mycom 320 SU-LX Booster Rotary Screw Compressor Package - 250 HP

Mfg: FES Mycom

Model: 320 SU-LX

Stock No: DTTC808

Serial No: 3231253

FES 775 / Mycom 320 SU-LX Booster Rotary Screw Compressor Package. Model: 320 SU-LX. S/N: 3231253. Contract numbers: EDE-0955 and EDE-9787. Drawing number: 11-0750-E2-1187 3/5. Refrigerant: R-717 (ammonia). Test pressure leak/hydrostatic: 313/470 psig. Nominal capacity: 254 tons with a -35 °F suction temperature and a 20 °F discharge temperature. Vi setting: 2.6. Displacement: 2,230 cfm. FES oil separator, S/N: 8320, Nat'l Bd: 1795, MAWP: 250 psi at 300 °F, MDMT: -20 °F, head radius: 2:1, heat thickness: 0.375 in., shell thickness: 0.375 in. Viking rotary pump, Model: AL4195, S/N: 11688064. Toshiba motor, 7.5 hp, 1165 rpm, 230/460 V, 20.0/10.0 amps, 60 Hz, 3 phase. Mycom Mypro-M control panel. Toshiba motor, 250 hp, 3540 rpm, 2300/4160 V, 59/33 amps, 60 Hz, 3 phase. Inlet: (1) 8 in. suction. Outlet: (1) 5 in. dia. discharge. Overall dimensions: 15 ft. 4 in. L x 5ft. W x 7ft. 4 in. H. (SR500) (ACN1192).











