

**2300 / 4000 V Reliance Electric Motor- 300 HP**

**Mfg: Reliance**

**Model:**

**Stock No.: DTTC809B**

**Serial No.:**

Reliance Electric Motor- 300 HP. Motor specifications: 3569 rpm, 2300 / 4000 V, 60 Hz, 3 phase. Continuous duty. Frame: 10EA5006S. Insulation class: F. Overall dimensions: 4 ft. L x 3 ft. 4 in. W x 2 ft. 6 in. H.



