

Frick Reciprocating Compressor- 100 HP

Mfg: Frick

Model: VSA 15x10

Stock No. DTTC824.

Serial No. 46776

Frick Reciprocating Compressor- 100 HP. Model: VSA 15x10. S/N: 46776. Capacity: 83 TR. Lubriquo, Inc. Box, Model: BOX-LUBE. Louis-Allis Motor, S/N: 2271242, motor specifications: 100 hp, 1760 rpm, 220/440 V, 246/123 amps, 60 Hz, 3 phase. Inlets: (1) 1/2 in. dia. port, (1) 5 in. dia. flanged port. Outlets: (1) 1/2 in. dia. port, (1) 1-1/2 in. dia. port, (1) 1 in. dia. port, (1) 5 in. dia. flanged port. Overall dimensions (motor): 41 in. L x 40 in. W x 30 in. H. Overall dimensions (compressor): 9 ft. 4-1/2 in. L x 48 in. W x 83 in. H.





