

FES 575B / Mycom 250L Screw Compressor Package - 700 HP

Mfg: FES Mycom

Model: 575B / 250L

Stock No.: DTTC831

Serial No.: 2512826

FES 575B / Mycom 250L Screw Compressor Package - 700 HP. Model: 575B / 250L. S/N: 2512826. Capacity: 570 TR. High stage compressor. Refrigerant: R-717. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. General Electric motor, 700 hp, 3575 rpm, 2400/4160 V, 154/89 amps, 60 Hz, 3 phase. Displacement: 1,670 cfm. E.L. Nickel oil separator, Model: C-1529, S/N: 21905, Nat'l Bd: 19934, MAWP: 250 psi @ 650 °F, MDMT: -20 °F. Viking rotary pump, Model: AK4195, S/N: 10851561. Baldor Super-E motor, 7-1/2 hp, 1180 rpm, 460 V, 10.5 amps, 60 Hz, 3 phase. Mycom Mypro-M control panel. Overall dimensions: 13 ft. L x 5 ft. 3 in. W x 8 ft. 2 in. H. (SR250) (ACN950). CF





