

**FES 385 / Mycom 250SUD-MX Screw Compressor Package - 500 HP**

**Mfg: FES Mycom**

**Model: 385 / 250SUD-MX**

**Stock No.: DTTC837**

**Serial No.: 2552007**

FES 385 / Mycom 250SUD-MX Screw Compressor Package - 500 HP. Model: 385 / 250SUD-MX. S/N: 2552007. Fixed Vi setting: 3.8. Displacement: 1,110 cfm. FES Oil Separator, S/N: 76042, Nat'l Bd: 166, MAWP: 250 psi, Maximum temperature: 300 °F, Minimum temperature: -20 °F. General Electric Motor, 500 hp, 3575 rpm, 2400/4160 V, 107/62 amps, 60 Hz, 3 phase. Viking Rotary Positive Displacement Pump, Model: AL4195, S/N: 5055550. U.S. Motor, 7.5 hp, 1155 rpm, 230/460 V, 22/11 amps, 60 Hz, 3 phase. Outlets: (1) 4 in. dia. refrigerant discharge. Overall dimensions: 11 ft. 11 in. L x 5 ft. 5 in. W x 7 ft. 3 in. H. (BC583-BC/Motor).



