

Stainless Steel Tandem Tabletop Conveyor

Mfg:

Model:

Stock No. DTWA353H.

Serial No.:

Stainless Steel Tandem Tabletop Conveyor. Conveyor 1- Maximum belt size handled: 4-1/2 in. W. Running gap for conveyor: 1-1/2 in. Sprocket diameter: 6 in. Pitch: 3/4 in. Conveyor 2- Maximum belt size handled: 4-1/2 in. W. Running gap for conveyor: 2-1/4 in. Sprocket diameter: 6 in. Pitch: 1-1/2 in. Reliance Electric Motor, 1-1/2 hp, 1725 rpm, 208-230/460-480 V, 5.6-5.6/2.8-3.0 amps, 60 Hz, 3 phase. Reeves Ultra Adjustable Speed Drive, size: 1B16, 62/7.7 rpm (max/min). Overall dimensions: 93 in. L x 26 in. W x 25-1/2 in. H.

