

**Chester Jensen Plate Heat Exchanger – 56.89 sq. ft.**


**Mfg: Chester Jensen**

**Model: NTFX**


**Stock No.: DWKN203.6**

**Serial No.: 6641386**

Chester Jensen Plate Heat Exchanger. Model: NTFX S/N: 6641386. Heat transfer surface area: 56.89 sq. ft. Approximate capacity using chilled water: 25 gph. (32) stainless steel plates, dimensions: 8 in. W x 2 ft. 8 in. H. Inlet and Outlets: 1-1/2 in. tri-clamp connections. Unit is mounted on a mobile base with a 30 gpm Wineman pump and 1-1/2 hp, 1750 rpm motor. Pump model: 1-1/4G-1/2-4. Overall dimensions: 2 ft. 10 in L x 2 ft. W x 4 ft. 4 in. H. (ACN106-64).







**MARATHON ELECTRIC**  
 MANUFACTURING CORP. WAUSAU, WISCONSIN

JK 56T170245A W HP 1/2  
 56-7 RPM 1725 PH 3 CY 60  
 208-220/440 F.LAMP. 275  
 TYPE T8 DUTY CONT AMB. 40 °C  
 S.P. 25 INSUL. CLASS A CODE

LOW VOLTAGE LINE HIGH VOLTAGE LINE

Ø1	Ø7	Ø13
Ø2	Ø8	Ø14
Ø3	Ø9	Ø15
Ø4	Ø10	Ø16
Ø5	Ø11	Ø17
Ø6	Ø12	Ø18