

APV Paraflow HX Plate Heat Exchanger Model 988

Mfg: APV

Model: HX

Stock No. ENDX750.3a

Serial No. M/C 988

APV Paraflow Plate Heat Exchanger. Model HX, S/N M/C 988. Stainless steel plates: (52). Heat transfer surface area: Approx. 84 sq. ft. Design pressure: 100 psig. Test pressure: 150 psig. Fixed end ports: (4) 2 in. Movable end ports: (4) 2 in. Terminal ports: (3) 2 in. Overall dimensions: 66 in. L x 24 in. W x 60 in. H.

