

## APV Positive Displacement Pump R-Series

Mfg: APV Crepaco

Model: R6R

Stock No. ERCS001.

Serial No. H-6034-94

APV Crepaco Positive Displacement Pump R-Series. Model: R6R. S/N: H-6034-94. Nominal capacity: 150 gpm @ 800 rpm. Displacement per 100 revolutions: 29 gpm. Motor with Reeves Variable Speed Module, size: 331, ratio: 6.2, output speeds: 520 rpm maximum, 104 rpm minimum. Complete parts interchangeable. Easy disassembly and cleanup, low maintenance. Typical applications: fruit cocktail, yogurt, alcoholic beverages, doughs, chocolate and shampoo. Inlet/outlets: (2) 3 in. S-line fittings. Overall dimensions: 3 ft. 8 in. L x 1 ft. 5 in. W x 3 ft. 2 in. H.



